



Tehničke karakteristike proizvoda

Karakteristike

EPH1800169

1P taster sa lokatorskom lampicom "svetlo", priključci bez zavrt., bez rama, bronza

Osnovne informacije

Serija	Asfora
Tip proizvoda ili komponente	Taster
Prezentacija uređaja	Mehanizam sa montažnim ramom
Broj prekidača	1
Nijansa boje	Bronzana
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža uređaja	Ugradno
Lokalna signalizacija	LED
Opseg snage	2300 W
Nazivna struja	10 A pri 250 V AC
Broj kablova	2 kabl(ovi) 2,5 mm ²
Krutost kabla	Fleksibilni Krući Jednožični višezični
Dužina ogoljenog dela žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna obrada	Ofarban
Provodni materijal	Bakar
Način fiksiranja	Zavrtnji ili kukice 51...70 mm
Povezivanje - priključci	Priključci bez zavrtneva
Označavanje	Simbol svetla
Širina	71 mm
Visina	71 mm
Dubina	43,0 mm
Projektovana dubina	15 mm
Masa proizvoda	0,0608 kg

Okruženje

Standardi	IEC 60669-1
Sertifikacija proizvoda	TSE[RETURN]VDE[RETURN]NF
Oznake kvaliteta	CE UKR
Ip stepen zaštite	IP20
Temperatura okoline za rad uređaja	-5...40 °C

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	7,500 cm
Package 1 Length	7,500 cm
Package 1 Weight	62,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	685,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	8,797 kg

Održivost ponude

Pakovanje sa recikliranim kartonom	Da
SCIP broj	C6de3800-7220-4403-a6a2-26e1f05e3f4b
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće