

Tehničke karakteristike proizvoda

Karakteristike

EPH1900321

Asfora - 1P taster-10A vijčani priključci,
lokatorska lampica, "stepenice", beli



Osnovne informacije

Serijski broj	Asfora
Tip proizvoda ili komponente	Taster
Prezentacija uređaja	Kompletan proizvod
Broj prekidača	1
Nijansa boje	Bela
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža uređaja	Ugradno
Lokalna signalizacija	LED
Opseg snage	2300 W
Nazivna struja	10 A pri 250 V AC
Broj kablova	2 kabl(ovi) 2,5 mm²
Krutost kabla	Fleksibilni Krti Jednožični višezični
Dužina ogoljenog dela žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna obrada	Sjajno
Provodni materijal	Bakar
Način fiksiranja	Zavrtnji ili kukice 51...70 mm
Povezivanje - priključci	Vijčani priključci
Označavanje	Simbol stepenica
Širina	83 mm
Visina	83 mm
Dubina	43,0 mm
Projektovana dubina	15 mm
Masa proizvoda	0,0759 kg

Okruženje

Standardi	IEC 60669-1
Sertifikacija proizvoda	VDE
Oznake kvaliteta	CE
Ip stepen zaštite	IP20
Temperatura okoline za rad uređaja	-5...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,300 cm
Package 1 Width	8,300 cm
Package 1 Length	4,300 cm
Package 1 Weight	85,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,400 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	989,000 kg
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	12619,000 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	У складу са изузецима
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------