



Tehničke karakteristike proizvoda

Karakteristike

EPH3100369

jednostruka utičnica sa uzemljenjem sa strane i
zaštitom, IP44, bronza

Osnovne informacije

| | |
|----------------------------------|----------------------|
| Serija | Asfora |
| Tip proizvoda ili komponente | Utičnica |
| Broj utičnica | 1 |
| Konfiguracija polova utičnice | 2P + E |
| Dodatne informacije | Poklopac i zaštita |
| Nijansa boje | Bronzana |
| Tip pakovanja | Pakovanje u kesicama |

Dopunske informacije

| | |
|----------------------------|--|
| Prezentacija uređaja | Kompletan proizvod |
| Montaža uređaja | Ugradno |
| Način fiksiranja | Zavrtnji ili kukice51...69 mm |
| Standard utičnice | CEE 7/3 |
| Outlet standard deviation | Šuko |
| Opis standarda utičnice | Uzemljenje sa strane |
| Opseg snage | 3680 W |
| Nazivna struja | 16 A pri 250 V AC |
| Završna obrada | Ofarban |
| Materijal | ABS (akrilonitril-butadien-stiren): dekorativni ram ABS + PC: centralna pločica ABS (akrilonitril-butadien-stiren): poklopac |
| Dužina ogoljenog dela žice | 13,0 mm |
| Provodni materijal | Bakar |
| Povezivanje - priključci | Vijčani priključci |
| Broj kablova | 2 kabl(ovi) 2,5 mm ² |
| Krutost kabla | Fleksibilni Krući Jednožični višežični |
| Količina po setu | 1 |
| Ip stepen zaštite | IP44 |
| Projektovana dubina | 17 mm |
| Širina | 83 mm |
| Visina | 83 mm |
| Dubina | 48 mm |
| Masa proizvoda | 0,104 kg |

Okruženje

| | |
|-------------------------|-----------------------------|
| Standardi | IEC 60884-1 |
| Sertifikacija proizvoda | TSE[RETURN]VDE[RETURN]Aenor |

Pakovanje

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4,500 cm |
| Package 1 Width | 8,000 cm |
| Package 1 Length | 8,000 cm |
| Package 1 Weight | 103,000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 9,500 cm |
| Package 2 Width | 18,500 cm |
| Package 2 Length | 27,500 cm |
| Package 2 Weight | 1,103 kg |
| Unit Type of Package 3 | S04 |
| Number of Units in Package 3 | 120 |
| Package 3 Height | 30,000 cm |
| Package 3 Width | 40,000 cm |
| Package 3 Length | 60,000 cm |
| Package 3 Weight | 13,847 kg |

Održivost ponude

| | |
|------------------------------------|---|
| Pakovanje bez plastike | Ne |
| Pakovanje sa recikliranim kartonom | Ne |
| SCIP broj | 52b60409-d705-46c7-9ba3-cc3ef6e307da |
| Uredba REACh | REACh Deklaracija |
| EU RoHS direktiva | Usaglašeno sa izuzecima |
| Bez žive | Da |
| Informacije o izuzeću od RoHS | Da |
| Kina RoHS regulacija | RoHS Deklaracija Za Kinu |
| WEEE | Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće |
| Povraćaj | No |