


Tehničke karakteristike proizvoda

Karakteristike

EPH5600123

Asfora - slepa maska - krem



Osnovne informacije

Grupa proizvoda	Asfora
Tip proizvoda ili komponente	Slepi poklopac
Prezentacija uređaja	Kompletan proizvod
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža uređaja	Ugradno
Materijal	ABS (akrilonitril-butadien-stiren): centralna pločica ABS (akrilonitril-butadien-stiren): dekorativni ram
Završna obrada	Sjajno
Način fiksiranja	Kukicama 51...80 mm
Visina	83 mm
Širina	83 mm
Dubina	35 mm
Projektovana dubina	9 mm
Masa proizvoda	0,052 kg

Okruženje

Ip stepen zaštite	IP20
-------------------	------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	8,000 cm
Package 1 Length	8,000 cm
Package 1 Weight	53,800 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	613,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm

Package 3 Length	60,000 cm
Package 3 Weight	7,894 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------