



# Tehničke karakteristike proizvoda

## Karakteristike

# EPH5810369

## Asfora - vertikalni ram za 3 elementa, bronza

### Osnovne informacije

|                              |                                    |
|------------------------------|------------------------------------|
| Grupa proizvoda              | Asfora                             |
| Grupa proizvoda              | Asfora                             |
| Tip proizvoda ili komponente | Dekorativni ram                    |
| Broj dvostrukih modula       | Trostruki                          |
| Pravac instalacije           | Vertikalno                         |
| Tip pakovanja                | Pakovanje u kesicama               |
| Nijansa boje                 | Bronzana                           |
| Materijal                    | ABS (akrilonitril-butadien-stiren) |
| Visina                       | 225 mm                             |

### Dopunske informacije

|                     |          |
|---------------------|----------|
| Završna obrada      | Sjajno   |
| Ip stepen zaštite   | IP20     |
| Širina              | 71 mm    |
| Dubina              | 9 mm     |
| Projektovana dubina | 9 mm     |
| Masa proizvoda      | 0,015 kg |

### Pakovanje

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1,000 cm  |
| Package 1 Width              | 9,000 cm  |
| Package 1 Length             | 23,000 cm |
| Package 1 Weight             | 29,000 g  |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 15        |
| Package 2 Height             | 9,500 cm  |
| Package 2 Width              | 18,500 cm |
| Package 2 Length             | 27,500 cm |
| Package 2 Weight             | 546,000 g |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 90        |
| Package 3 Height             | 30,000 cm |
| Package 3 Width              | 30,000 cm |
| Package 3 Length             | 40,000 cm |
| Package 3 Weight             | 3,592 kg  |

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

## Održivost ponude

|                                    |  |
|------------------------------------|--|
| Pakovanje bez plastike             | Ne   |
| Pakovanje sa recikliranim kartonom | Ne   |
| SCIP broj                          | C6de3800-7220-4403-a6a2-26e1f05e3f4b   |
| Uredba REACH                       | <a href="#">REACH Deklaracija</a>  |
| Bez SVHC-a REACH                   | Da   |
| EU RoHS direktiva                  | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) <a href="#">EU RoHS deklaracija</a> |
| Bez toksičnih teških metala        | Da   |
| Bez žive                           | Da   |
| Informacije o izuzeću od RoHS      | <a href="#">Da</a>   |
| Kina RoHS regulacija               | <a href="#">RoHS Deklaracija Za Kinu</a>   |
| Izjava o zaštiti okoline           | <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>  |
| Profil cirkularnosti               | Nema potrebe za namenskim operacijama recikliranja   |
| Povraćaj                           | No   |