



# Tehničke karakteristike proizvoda

## Karakteristike

# EPH9900169

Asfora - dvostruka utičnica - sa uzemljenjem sa strane, bez rama, bronza

### Osnovne informacije

Serija	Asfora
Tip proizvoda ili komponente	Utičnica
Broj utičnica	2
Konfiguracija polova utičnice	2P + E
Nijansa boje	Bronzana
Tip pakovanja	Pakovanje u kesicama

### Dopunske informacije

Prezentacija uređaja	Kompletan proizvod
Montaža uređaja	Ugradno
Način fiksiranja	Kukicama54...72 mm
Standard utičnice	CEE 7/3
Outlet standard deviation	Šuko
Opis standarda utičnice	Uzemljenje sa strane
Opseg snage	3680 W
Nazivna struja	16 A pri 250 V AC
Završna obrada	Ofarban
Materijal	ABS (akrilonitril-butadien-stiren): dekorativni ram ASA + PC: centralna pločica
Dužina ogoljenog dela žice	11 mm
Provodni materijal	Bakar
Povezivanje - priključci	Vijčani priključci
Broj kablova	2 kabl(ovi) 2,5 mm <sup>2</sup>
Krutost kabla	Jednožični višežični Krti Fleksibilni
Količina po setu	1
Ip stepen zaštite	IP20
Projektovana dubina	23 mm
Širina	83 mm
Visina	123 mm
Dubina	46 mm

### Okruženje

Standardi	IEC 60884-1
Sertifikacija proizvoda	VDE[RETURN]Aenor[RETURN]UKR

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,500 cm
Package 1 Width	8,500 cm
Package 1 Length	12,500 cm
Package 1 Weight	103,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10,000 cm
Package 2 Width	20,500 cm
Package 2 Length	31,000 cm
Package 2 Weight	1,127 kg
Unit Type of Package 3	S04
Number of Units in Package 3	50
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	5,981 kg

## Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Ne
SCIP broj	40edb622-a740-45db-a8a3-3e1ee644be35
Uredba REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No