

Tehničke karakteristike proizvoda

Karakteristike

ETK25350

Ultra - T račva - 25 x 16/25 mm - ABS - beli



Osnovne informacije

Grupa proizvoda	Ultra
Tip proizvoda ili komponente	T element
Primena uređaja	Kablovski razvod
Nijansa boje	Bela (RAL 9010)
Količina po setu	Set od 40

Dopunske informacije

Dimenzije parapetnog razvoda	25 x 25 mm 25 x 16 mm
Materijal parapetnog razvoda	Plastika
Način pričvršćivanja	Zatvaranje sa klikom
Materijal	ABS termoplastični orman
Visina	45 mm
Širina	65 mm
Dubina	27 mm

Okruženje




Standardi	EN 50085-1:2005 EN 50085-2-1:2006
Temperatura okoline za rad uređaja	-5...60 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,000 cm
Package 1 Width	4,500 cm
Package 1 Length	6,000 cm
Package 1 Weight	9,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	40
Package 2 Height	13,000 cm
Package 2 Width	14,000 cm
Package 2 Length	17,000 cm
Package 2 Weight	433,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	640
Package 3 Height	30,000 cm

Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	7,564 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 months
-----------	-----------