

Tehničke karakteristike proizvoda

Karakteristike

ETK40350

Ultra - T račva - 40 x 16/25/40 mm - ABS - bela



Osnovne informacije

Grupa proizvoda	Ultra
Tip proizvoda ili komponente	T element
Primena uređaja	Kablovski razvod
Nijansa boje	Bela (RAL 9010)
Količina po setu	Set od 40

Dopunske informacije

Dimenzije parapetnog razvoda	40 x 16 mm 40 x 25 mm 40 x 40 mm
Materijal parapetnog razvoda	Plastika
Način pričvršćivanja	Zatvaranje sa klikom
Materijal	ABS termoplastični orman
Visina	60 mm
Širina	77 mm
Dubina	41 mm

Okruženje

Standardi	EN 50085-1:2005 EN 50085-2-1:2006
Temperatura okoline za rad uređaja	-5...60 °C
Ip stepen zaštite	IP40
Ik stepen zaštite	IK07

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	6,000 cm
Package 1 Length	8,000 cm
Package 1 Weight	18,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	40
Package 2 Height	11,000 cm
Package 2 Width	20,500 cm
Package 2 Length	28,000 cm
Package 2 Weight	881,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	280

Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	6,755 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------