

Tehničke karakteristike proizvoda Karakteristike

GV2G454

Linergy FT - češljasta sabirnica - 63 A - 4
otcepa - 54 mm razmak



Osnovne informacije

Grupa proizvoda	Linergy
Ime proizvoda	FT
Kratko ime uređaja	GV2G
Tip proizvoda ili komponente	Češljasta sabirnica
Pribor / posebna kategorija	Pribor za povezivanje
Broj polova	3P
Kompatibilnost grupe proizvoda	TeSys Deca TeSys GV2 TeSys K TeSys U
Broj otcepa	4
[ith] dozvoljena termička struja u vazduhu	63 A
Povezivanje	54 mm

Dopunske informacije

Lokacija za montiranje	Na priključku
[ui] nazivni napon izolacije	690 V
Dužina	206 mm
Masa proizvoda	0,085 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1,900 cm
Package 1 Width	3,700 cm
Package 1 Length	21,600 cm
Package 1 Weight	88,000 g
Unit Type of Package 2	S01
Number of Units in Package 2	50
Package 2 Height	15,000 cm
Package 2 Width	15,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,628 kg
Unit Type of Package 3	P06
Number of Units in Package 3	1600
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	156,500 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	REACH Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka

Ugovorna garancija

Garancija	18 months
-----------	-----------