

Tehničke karakteristike proizvoda Karakteristike

GZ1AU225 podnaponski okidač GZ1-AU - 220..240 V AC 50 Hz



Osnovne informacije

Grupa proizvoda	Easy TeSys
Tip proizvoda ili komponente	Podnaponski okidač
Primena uređaja	Zaštita

Dopunske informacije

Kompatibilnost grupe proizvoda	Easypact EasyPact TVS GZ1E prekidač
Napon upravljačkog kola	220...240 V AC 50 Hz
Povezivanje - priključci	Vijčani priključni blokovi
Visina	89 mm
Širina	18 mm
Dubina	66 mm
Masa proizvoda	0,105 kg

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,500 cm
Package 1 Width	8,500 cm
Package 1 Length	9,000 cm
Package 1 Weight	113,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	42
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	4,884 kg
Unit Type of Package 3	P06
Number of Units in Package 3	672
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	87,144 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.