



Tehničke karakteristike proizvoda

Karakteristike

ISM20100

OptiLine 45 - stub - montiranje pritezanjem -
jednostrani - anod. - 2700-3100 mm



Osnovne informacije

Range	OptiLine
Ime proizvoda	OptiLine 45
Oblik	Ovalni
Kablovski instalacioni sistem	Stub
Product type	Stub
Prezentacija uređaja	Prazno
Tip stuba	Jednostrano
Završna obrada stuba/ stubića	Anodička oksidacija
Način montaže stuba	Napregnut
Podšavanje	Podšavanje po visini: 400 mm

Dopunske informacije

Additional information	Podesivost plafonskih nosača 400 mm
Colour	Prirodna
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum anodička oksidacija
Quantity package 1 / unit	Set od 1
Visina	2700...3100 mm
Dubina	89 mm
Širina	68 mm
Tip poklopca	1 zatvoreni poklopac cover 45 mm in aluminijum anodička oksidacija
Useful cross section	442 mm ²
Podela odeljaka	1 odeljak

Okruženje





Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12,500 cm
Package 1 Width	16,300 cm
Package 1 Length	291,500 cm
Package 1 Weight	7,500 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	28
Package 2 Height	68,500 cm
Package 2 Width	120,000 cm
Package 2 Length	400,000 cm
Package 2 Weight	230,000 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------