



Tehničke karakteristike proizvoda

Karakteristike

ISM20116

OptiLine 45 - stub - pokretni - dvostrani - anod. - 2450 mm



Osnovne informacije

Range	OptiLine
Ime proizvoda	OptiLine 45
Kablovski instalacioni sistem	Stub
Product type	Stub
Tip stuba	Dvostrano
Završna obrada stuba/ stubića	Anodička oksidacija
Način montaže stuba	Slobodnostojeći

Dopunske informacije

Colour	Prirodna
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum anodička oksidacija
Quantity package 1 / unit	Set od 1
Visina	2450 mm
Dubina	90 mm
Širina	116 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16,000 cm
Package 1 Width	29,000 cm
Package 1 Length	272,000 cm
Package 1 Weight	9,000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	20
Package 2 Height	94,000 cm
Package 2 Width	120,000 cm
Package 2 Length	370,000 cm
Package 2 Weight	208,000 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------