



Tehničke karakteristike proizvoda

Karakteristike

ISM20119P

OptiLine 45 - stub - samostojeći - dvostrani -
polarno bela - 2900 mm



Osnovne informacije

Range	OptiLine
Ime proizvoda	OptiLine 45
Kablovski instalacioni sistem	Stub
Product type	Stub
Tip stuba	Dvostrano
Završna obrada stuba/ stubića	Presvučen prahom
Način montaže stuba	Slobodnostojeći

Dopunske informacije

Colour	Polarno bela (RAL 9003)
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum presvučen prahom
Quantity package 1 / unit	Set od 1
Visina	2900 mm
Dubina	90 mm
Širina	116 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
Ip stepen zaštite	IP40

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	290,0 cm
Package 1 Width	11,6 cm
Package 1 Length	9,0 cm
Package 1 Weight	11,22 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Height	12,7 cm
Package 2 Width	15,5 cm
Package 2 Length	302,0 cm
Package 2 Weight	11,717 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	28
Package 3 Height	64,9 cm
Package 3 Width	120,0 cm
Package 3 Length	370,0 cm
Package 3 Weight	349,076 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja