



Tehničke karakteristike proizvoda

Karakteristike

ISM20201P

OptiLine 45 - stub - jednostran - polarno bela -
700 mm



Osnovne informacije

Grupa proizvoda	OptiLine 45
Kablovski instalacioni sistem	Stubić
Product type	Stubić
Prezentacija uređaja	Prazno
Tip stuba	Jednostrani
Završna obrada stuba/ stubića	Presvučen prahom

Dopunske informacije

Colour	Polarno bela (RAL 9003)
Način pričvršćivanja	Pričvršćivanje zavrtnjem
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum presvučen prahom
Quantity package 1 / unit	Set od 1
Visina	89 mm
Širina	68 mm

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN-AW-6063 NF C 68-102
Operating temperature	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	70,0 cm
Package 1 Width	6,8 cm
Package 1 Length	8,9 cm
Package 1 Weight	1,74 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Height	13,1 cm
Package 2 Width	16,1 cm
Package 2 Length	72,9 cm
Package 2 Weight	2,165 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	28
Package 3 Height	67,4 cm
Package 3 Width	80,0 cm
Package 3 Length	120,0 cm
Package 3 Weight	80,62 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja