



Tehničke karakteristike proizvoda

Karakteristike

ISM20202

OptiLine 45 - stubić - dvostrani - anodizirani -
700 mm



Osnovne informacije

Grupa proizvoda	OptiLine 45
Kablovski instalacioni sistem	Stubić
Product type	Stubić
Tip stuba	Dvostrani
Završna obrada stuba/ stubića	Anodička oksidacija

Dopunske informacije

Colour	Prirodna
Način pričvršćivanja	Pričvršćivanje zavrtnjem
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum anodička oksidacija
Quantity package 1 / unit	Set od 1
Visina	700 mm
Širina	116 mm
Segment tržišta	Male komercijalne zgrade Stambene zgrade

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN-AW-6063 NF C 68-102
Operating temperature	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13,0 cm
Package 1 Width	16,0 cm
Package 1 Length	74,5 cm
Package 1 Weight	2,9 kg
Unit Type of Package 2	P12
Number of Units in Package 2	28
Package 2 Height	67,0 cm
Package 2 Width	80,0 cm
Package 2 Length	120,0 cm
Package 2 Weight	91,0 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH free of SVHC	Yes
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Izjava o zaštiti životne sredine	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------