

Tehničke karakteristike proizvoda Karakteristike

LA4SKE1E

TeSys SK - modul za prigušenje - varistor -
24...48 V AC/DC



Osnovne informacije

Grupa proizvoda	TeSys
Kratko ime uređaja	LA4SK
Tip proizvoda ili komponente	Prigušivač
Kompatibilnost proizvoda	CA2SK LC1SK06 CA3SK LC1SKGC LP1SK06
Tehnologija prigušenja	Varistor (ograničenje vršnog napona)
Količina po setu	Set od 10

Dopunske informacije

Lokacija za montiranje	Desna strana
[Uc] control circuit voltage	24...48 V AC 24...48 V DC
Maksimalni vršni napon	2 Uc
Masa proizvoda	0,003 kg

Okruženje

Temperatura okoline za rad uređaja	-20...50 °C
Temperatura okoline za skladištenje	-50...70 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,0 cm
Package 1 Width	5,0 cm
Package 1 Length	12,0 cm
Package 1 Weight	2,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4,0 cm
Package 2 Width	5,0 cm
Package 2 Length	12,0 cm
Package 2 Weight	28,0 g
Unit Type of Package 3	S01
Number of Units in Package 3	190
Package 3 Height	15,0 cm
Package 3 Width	15,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	767,0 g

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	У складу са изузецима
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

Ugovorna garancija

Garancija	18 meseci
-----------	-----------