

Tehničke karakteristike proizvoda Karakteristike

LC1E3810P7
Contactor, EasyPact
TVS, 3P(3NO), AC-3, ≤440V, 38A, 230V AC
coil, 1NO auxiliary contact



Osnovne informacije

Grupa proizvoda	Easy TeSys
Grupa proizvoda	Easy TeSys Control
Tip proizvoda ili komponente	Kontaktor
Kratko ime uređaja	LC1E

Dopunske informacije

Moment pritezanja	Upravljačko kolo: 1,2 N.m Kolo napajanja: 2,1 N.m
-------------------	--

Okruženje

Dopustiva temperatura u okolini uređaja	-20...70 °C na Uc -60...80 °C storage -5...55 °C radno
---	--

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,500 cm
Package 1 Width	8,500 cm
Package 1 Length	9,000 cm
Package 1 Weight	458,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	24
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	11,364 kg
Unit Type of Package 3	P06
Number of Units in Package 3	384
Package 3 Height	75,000 cm
Package 3 Width	60,000 cm
Package 3 Length	80,000 cm
Package 3 Weight	189,824 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.