

# Tehničke karakteristike proizvoda

## Karakteristike

# LMR0100003

## Easy Styl, prekidač, 1P, 1 modul, crni



### Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam
Funkcija prekidača	Jednopolni izborni
Broj modula	1 modul
Broj prekidača	1
Izvršni organ	Preklopni prekidač
Primena uređaja	Upravljanje
Kompatibilnost grupe proizvoda	Easy Styl
Način pričvršćivanja	Klikom
Nijansa boje	Crna (RAL 9005)
Završna obrada	Sjajno
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	16 AX pri 250 V AC 50/60 Hz
Kapacitet priključaka	<= 2 x 2.5 mm <sup>2</sup> za jednožični ili fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	10...12,5 mm
Materijal	ABS + PC
Visina	51 mm
Širina	22 mm
Dubina	35 mm
Masa proizvoda	0,018 kg
Standardi	EN/IEC 60669-1
Sertifikacije proizvoda	TSE
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

### Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,000 cm
Package 1 Width	3,000 cm
Package 1 Length	5,000 cm
Package 1 Weight	20,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	5,500 cm
Package 2 Width	12,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	428,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	240
Package 3 Height	30,000 cm

Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	5,400 kg

## Održivost ponude

EU RoHS direktiva	Na ispitivanju
-------------------	----------------