

Tehničke karakteristike proizvoda Karakteristike

LMR0124003

Easy Styl, prekidač, 1P naizmenični, 2 modula, crni



Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam
Funkcija prekidača	Jednopolni naizmenični
Broj modula	2 modula
Izvršni organ	Preklopni prekidač
Primena uređaja	Upravljanje
Kompatibilnost grupe proizvoda	Easy Styl
Način pričvršćivanja	Klikom
Nijansa boje	Crna (RAL 9005)
Završna obrada	Sjajno
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	16 AX pri 250 V AC 50/60 Hz
Kapacitet priključaka	<= 2 x 2.5 mm ² za jednožični ili fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	10... 12,5 mm
Materijal	ABS + PC
Visina	51 mm
Širina	44 mm
Dubina	34 mm
Standardi	EN/IEC 60669-1
Sertifikacije proizvoda	TSE
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	4,500 cm
Package 1 Length	4,500 cm
Package 1 Weight	26,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,500 cm
Package 2 Width	12,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	303,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm

Package 3 Length	60,000 cm
Package 3 Weight	3,947 kg

Održivost ponude

EU RoHS direktiva	Na ispitivanju
-------------------	----------------