

Tehničke karakteristike proizvoda

Karakteristike

LMR0130001

Easy Styl, taster, sa simbolom zvona, 1 modul, beli



Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Taster
Prezentacija uređaja	Mehanizam
Broj modula	1 modul
Izvršni organ	Taster
Primena uređaja	Prekidač za zvono
Kompatibilnost grupe proizvoda	Easy Styl
Način pričvršćivanja	Klikom
Nijansa boje	Bela (RAL 1015)
Završna obrada	Sjajno
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	10 A pri 250 V AC 50/60 Hz
Kapacitet priključaka	$\leq 2 \times 2.5 \text{ mm}^2$ za jednožični ili fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	10...12,5 mm
Materijal	ABS + PC
Visina	51 mm
Širina	22 mm
Dubina	35 mm
Standardi	EN/IEC 60669-1
Sertifikacije proizvoda	TSE
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,000 cm
Package 1 Width	3,500 cm
Package 1 Length	4,500 cm
Package 1 Weight	19,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	5,500 cm
Package 2 Width	12,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	402,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	240
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	4,941 kg

