

Tehničke karakteristike proizvoda

Karakteristike

LMR0220004

Easy Styl, taster, za upravljanje, 2 modula,
srebrni



Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Taster
Prezentacija uređaja	Mehanizam
Broj modula	2 modula
Izvršni organ	Taster
Primena uređaja	Upravljanje
Kompatibilnost grupe proizvoda	Easy Styl
Način pričvršćivanja	Klikom
Nijansa boje	Srebrna
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	10 A pri 250 V AC 50/60 Hz
Kapacitet priključaka	$\leq 2 \times 2.5 \text{ mm}^2$ za jednožični ili fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	10...12,5 mm
Materijal	ABS + PC
Visina	51 mm
Širina	22 mm
Dubina	34 mm
Standardi	EN/IEC 60669-1
Sertifikacije proizvoda	TSE
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,500 cm
Package 1 Width	4,500 cm
Package 1 Length	5,000 cm
Package 1 Weight	24,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,500 cm
Package 2 Width	12,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	282,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	3,648 kg

Održivost ponude

EU RoHS direktiva

Na ispitivanju