

Tehničke karakteristike proizvoda

Karakteristike

LMR1401002

Easy Styl, prekidač, 1P, 1 modul, krem



Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam
Funkcija prekidača	Jednopolni izborni
Broj modula	1 modul
Broj prekidača	1
Izvršni organ	Preklopni prekidač
Primena uređaja	Upravljanje
Kompatibilnost grupe proizvoda	Easy Styl
Način pričvršćivanja	Klikom
Nijansa boje	Krem
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	16 AX pri 250 V AC 50/60 Hz
Kapacitet priključaka	$\leq 2 \times 2.5 \text{ mm}^2$ za jednožični ili fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	10...12,5 mm
Materijal	ABS + PC
Visina	51 mm
Širina	22 mm
Dubina	35 mm
Standardi	EN/IEC 60669-1
Sertifikacije proizvoda	TSE
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,500 cm
Package 1 Width	3,500 cm
Package 1 Length	4,500 cm
Package 1 Weight	21,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	6,000 cm
Package 2 Width	12,500 cm
Package 2 Length	24,000 cm
Package 2 Weight	466,000 g
Unit Type of Package 3	S03
Number of Units in Package 3	240
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm

Package 3 Length	40,000 cm
Package 3 Weight	6,544 kg

Održivost ponude

EU RoHS direktiva	Na ispitivanju
-------------------	----------------