

Tehničke karakteristike proizvoda

Karakteristike

LMR5510003

Easy Styl, utičnica, 2P, 1 modul, crna



Osnovne informacije

Grupa proizvoda	Easy Styl
Grupa proizvoda	Easy Styl
Tip proizvoda ili komponente	Utičnica
Broj energetskih utičnica	1
Prezentacija uređaja	Mehanizam
Kompatibilnost grupe proizvoda	Easy Styl
Konfiguracija polova utičnice	2P
Standard utičnice	Evropski i američki
Opis standarda utičnice	Bez kontakta uzemljenja
Broj modula	1 modul
Nijansa boje	Crna
Tip pakovanja	Pakovanje u kesicama
Nazivna struja	10 A pri 230/250 V AC 50 Hz
Povezivanje - priključci	Vijčani priključni blokovi
Materijal	ABS + PC
Visina	51 mm
Širina	22 mm
Dubina	45 mm
Masa proizvoda	0,021 kg
Ik stepen zaštite	IK01
Ip stepen zaštite	IP20

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,000 cm
Package 1 Width	3,000 cm
Package 1 Length	5,000 cm
Package 1 Weight	19,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	5,500 cm
Package 2 Width	12,000 cm
Package 2 Length	24,000 cm
Package 2 Weight	426,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	240
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	5,369 kg

