

# Tehničke karakteristike proizvoda

## Karakteristike

# LSS100200

## spaceLYnk kontroler



### Osnovne informacije

Grupa proizvoda	KNX
Ime proizvoda	SpaceLYnk
Tip proizvoda ili komponente	Logički kontroler

### Dopunske informacije

Protokol komunikacionog porta	Modbus IP (Internet Protocol) BACnet KNX
[us] nazivni napon napajanja	24 V DC
Potrošnja	2 W
LED indikator	ZaCPU opterećenje: LED (zelen) ZaKNX napojen/resetovan: LED (zelen/crvena)
Fizički interfejs	1 EcoStruxure EV Charging Expert 1 RS485 1 RS232 1 TP-UART2
Ethernet port	10BASE-T/100BASE-TX
Integrirani načini povezivanja	1 USB 2.0 port
Tip upravljanja	RESET taster
Povezivanje - priključci	KNX bus: bus priključak 2 kabl(ovi) 0,8 mm <sup>2</sup> Napajanja: vijčani priključak 1,5 mm <sup>2</sup> Serijska veza: vijčani priključak 1,5 mm <sup>2</sup>
Nosači za montažu	DIN šina
Visina	90 mm
Širina	52 mm
Dubina	58 mm

### Okruženje

Temperatura okoline za rad uređaja	-5...45 °C
Nadmorska visina za rad	<= 2000 m
Relativna vlažnost	0...93 %
Ip stepen zaštite	IP20
Standardi	IEC 60950-1

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova poveznica ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,000 cm
Package 1 Width	7,000 cm
Package 1 Length	9,300 cm
Package 1 Weight	125,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7,500 cm
Package 2 Width	20,000 cm
Package 2 Length	35,000 cm
Package 2 Weight	1,371 kg
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	5,965 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.