



### Osnovne informacije

Grupa proizvoda	Compact
Grupa proizvoda	ComPact NSX100...250
Tip proizvoda ili komponente	Zaštitna jedinica
Ime zaštitne jedinice	TM-D
Tehnologija zaštitne jedinice	Termomagnetna
Kompatibilnost grupe proizvoda	Compact NSX160 Compact NSX250
Primena uređaja	Razvod električne energije
Number of poles	4P
Opis zaštićenih polova	3t
Pozicija nultog provodnika	Levo
Funkcija zaštitne jedinice	Li
Tip zaštite	L : for zaštita od preopterećenja (termičkog) I : for zaštita od kratkog spoja
Trip unit rated current	125 A pri 40 °C
[ue] nazivni napon	690 V AC 50/60 Hz
Tip mreže	AC
Mrežna frekvencija	50/60 Hz

### Dopunske informacije

Long-time pick-up adjustment type Ir (thermal protection)	Podesivo
[Ir] long-time protection pick-up adjustment range	0.7...1 x In
Long-time protection delay adjustment type tr	Fiksno
[tr] long-time protection delay adjustment range	120...400 Sekundi pri 1.5 x In 15 sekundi pri 6 x Ir
Short-time protection pick-up adjustment type Isd	Fiksno
[Isd] Short-time protection pick-up adjustment range	1250 A
Short-time protection delay adjustment type tsd	Fiksno
Diferencijalna zaštita	Bez
Neutral protection settings	Bez zaštite

### Okruženje

Standardi	EN/IEC 60947-2 UL 508
Sertifikacija proizvoda	EAC Marine CCC
Temperatura okoline za rad uređaja	-25...70 °C
Temperatura okoline za skladištenje	-50...85 °C

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenevidenih informacija.

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,5 cm
Package 1 Width	9,5 cm
Package 1 Length	14,8 cm
Package 1 Weight	499,0 g
Unit Type of Package 2	S03
Number of Units in Package 2	23
Package 2 Height	30,0 cm
Package 2 Width	30,0 cm
Package 2 Length	40,0 cm
Package 2 Weight	11,8 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez žive	Da
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	<a href="#">Informacije O Kraju Radnog Veka</a>
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------