



Tehničke karakteristike proizvoda

Karakteristike

LV434063

modul I/O (6DI, 3O/P, 1AI)

Osnovne informacije

| | |
|--------------------------------|--|
| Kratko ime uređaja | I/O |
| Tip proizvoda ili komponente | I/O modul |
| Kompatibilnost grupe proizvoda | Masterpact Masterpact MTZ Masterpact Masterpact NT Masterpact Masterpact NW Compact Compact NSX Compact Compact NS630b...1600 Compact Compact NS1600b...3200 PowerPact PowerPact J PowerPact PowerPact L PowerPact PowerPact H PowerPact PowerPact P PowerPact PowerPact H |
| Ime proizvoda | Enerlin'X IO |

Dopunske informacije

| | |
|--------------------------------|--|
| Tip komunikacije | Universal Logic Plug na 2 RJ45 konektora |
| [us] nazivni napon | 24 V DC - 20...10 % |
| Struja potrošnje | 165 mA |
| Elektromagnetna kompatibilnost | Test otpornosti elektrostatičkog pražnjenja u skladu sa EN/IEC 61000-4-2 Otpornost na emisije vezane sa zračenjem 10 V/m u skladu sa EN/IEC 61000-4-3 Test otpornosti udara u skladu sa EN/IEC 61000-4-5 |
| Broj ulaza | 6 digitalni 1 analogni |
| Tip ulaza | Digitalni pri stanje 1: 19,8...25,2 V - DC - 6,1...8,8 mA Digitalni pri stanje 0: 0...19,8 V - DC - 0 mA |
| Broj izlaza | 3 digitalni |
| Tip izlaza | Digitalni: 250 V - AC - 5 A |
| Dužina kabla | 10 m |
| Način montiranja | Stezaljkom |
| Nosači za montažu | 35 mm DIN šina |
| Tip upravljanja | Putem softvera |
| Kašnjenje | 0...20 s |
| Frekvencija vibracija | 5...8,4 Hz |
| Povezivanje - priključci | Vijčani priključni blok |
| Sertifikacija proizvoda | FCC[RETURN]GOST[RETURN]CE[RETURN]cULus |
| Standardi | IEC 60947-6-2 UL 60950 IEC 60950 UL 508 |
| Dubina | 70,6 mm |
| Visina | 116 mm |
| Širina | 71,7 mm |
| Masa proizvoda | 229,5 g |

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovenavedenih informacija.





Okruženje

| | |
|-------------------------------------|---|
| Relativna vlažnost | 5...85 % |
| Ip stepen zaštite | IP2x priključci: IP4X prednji panel: IP3x drugi delovi: |
| Temperatura okoline za rad uređaja | -20...70 °C |
| Temperatura okoline za skladištenje | -40...85 °C |
| Stepen zaprljanosti | 3 |
| Otpornost na plamen | V0 u skladu sa UL |
| Otpornost na udar | 1000 m/s ² |

Pakovanje

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9,000 cm |
| Package 1 Width | 8,800 cm |
| Package 1 Length | 12,500 cm |
| Package 1 Weight | 294,000 g |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 24 |
| Package 2 Height | 30,000 cm |
| Package 2 Width | 30,000 cm |
| Package 2 Length | 40,000 cm |
| Package 2 Weight | 7,752 kg |
| Unit Type of Package 3 | P06 |
| Number of Units in Package 3 | 192 |
| Package 3 Height | 75,000 cm |
| Package 3 Width | 60,000 cm |
| Package 3 Length | 80,000 cm |
| Package 3 Weight | 71,228 kg |

Održivost ponude

| | |
|------------------------------------|--|
| SCIP broj | 2fc07de3-36e3-4c4f-8b40-e79c0322200e |
| Pakovanje bez plastike | Ne |
| Pakovanje sa recikliranim kartonom | Ne |
| BVB |  Prihvaćeno |
| Uredba REACH |  REACH Deklaracija |
| EU RoHS direktiva | Usaglašeno sa izuzecima |
| Bez žive | Da |
| Kina RoHS regulacija |  RoHS Deklaracija Za Kinu |
| Informacije o izuzeću od RoHS |  Da |
| WEEE | Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće |
| Performanse sadržaja halogena | Proizvod sadrži halogen iznad dozvoljenog nivoa |
| Povraćaj | No |
| Emisija ugljenika (kg CO2 eq.) | 38 |

Ugovorna garancija

| | |
|-----------|-----------|
| Garancija | 18 months |
|-----------|-----------|