

Tehničke karakteristike proizvoda Karakteristike

MIP82212

Mini Pragma dozna - 2 x 12 modula - ugradna



Osnovne informacije

Grupa proizvoda	Resi9
Tip proizvoda ili komponente	Baza
Pribor / posebna kategorija	Pribor ormana
Kompatibilnost grupe proizvoda	Resi9 Resi9 MP
[in] nazivna struja	63 A
Nb of horizontal rows	2
Nb of 18 mm modules per row	12
Broj priključnih blokova	1 uzemljenje (zavrtanj) sa 16 izvodi 1 nula (zavrtanj) sa 16 izvodi
Funkcija priključnog bloka	Uzemljenje/nula

Dopunske informacije

Montaža ormana	Ugradna
9 mm redovi	4
Ukupan broj 18 mm modula	24
Kablovski uvod	Predefinisani otvori
Izvodi razvodnog bloka	2 x 16 mm ² za uzemljenje 2 x 16 mm ² za nula 6 x 6 mm ² za uzemljenje 6 x 6 mm ² za nula 8 x 10 mm ² za uzemljenje 8 x 10 mm ² za nula
Materijal kućišta	Zadnji deo: tehno plastika
Širina	Zid: 270 mm
Visina	Zid: 353 mm
Dubina	Zid : 80 mm Spoljašnja strana : 18 mm Ukupno : 98 mm

Okruženje

Standardi	IEC 60695-2-11 EN 50102
Otpornost na vatru	Zadnji deo: 650 °C
Ik stepen zaštite	IK07
Temperatura okoline za rad uređaja	-25...60 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	27 cm
Package 1 Length	35,3 cm
Package 1 Weight	814 g

Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	52 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5,798 kg
Unit Type of Package 3	P12
Number of Units in Package 3	112
Package 3 Height	120 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	104,768 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Učinak u vezi sa sadržajem halogena	Proizvod bez halogena

Ugovorna garancija

Garancija	18 months
-----------	-----------