



Tehničke karakteristike proizvoda

Karakteristike

MVS21430

EasyCom komunikacioni modul za EasyPact MVS

Osnovne informacije

Grupa proizvoda	EasyPact MVS
Kratko ime uređaja	EasyCom
Tip proizvoda ili komponente	Komunikacioni modul
Kompatibilnost grupe proizvoda	EasyPact MVS

Dopunske informacije

Broj ulaza	9 digitalni 1 analogni
Broj izlaza	6 digitalni
Tip komunikacije	Modbus
Način montiranja	Fiksno
Nosači za montažu	DIN šina
Položaj na uređaju	Osnovni ram
[us] nazivni napon	24 V DC - 20...10 %
Potrošnja	3,96 W
Povezivanje - priključci	Vijčani priključni blokovi

Okruženje

Stepen zaprljanosti	3
---------------------	---

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,000 cm
Package 1 Width	9,500 cm
Package 1 Length	15,000 cm
Package 1 Weight	304,000 g
Unit Type of Package 2	S04
Number of Units in Package 2	32
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm
Package 2 Weight	10,325 kg
Unit Type of Package 3	P12
Number of Units in Package 3	128
Package 3 Height	45,000 cm
Package 3 Width	80,000 cm

Package 3 Length	120,000 cm
Package 3 Weight	53,300 kg

Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Da
SCIP broj	3f2d539a-6ab5-46aa-8603-9354f4ae3294
Uredba REACh	REACh Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Bez PVC-a	Da
Povraćaj	No