

Tehničke karakteristike proizvoda

Karakteristike

NSYDLR36

modularno kućište DLCR tip za Spacial WM čelični orman, 36 modula, V400xŠ300



Osnovne informacije

Grupa proizvoda	PanelSeT
Pribor / posebna kategorija	Pribor za montažu
Application	Modularni razvod električne energije Više namena
Tip proizvoda ili komponente	Šasija
Kratko ime uređaja	DL
For enclosure nominal dimensions	-
Lokacija za montiranje	Prednja strana ormara
Kompatibilnost grupe proizvoda	Spacial Spacial S3X PanelSeT PanelSeT CRN
Sastav uređaja	1 konstrukcija šasije 1 sabirnica nule/uzemljenja 2 x 16 mm ² 5 x 6 mm ² 1 prednji panel 3 35 mm DIN šina
Količina po setu	Set od 1

Dopunske informacije

Materijal	Čelik
Boja	Prednji panel: siva (RAL 7035)
Završna obrada	Poliesterski prah
Način fiksiranja	Sa elementom za fiksiranje - na zadnjem delu sa nosačima lokacija
Podešavanje	U visinu od 40 do 85 mm za DIN šinu
Broj horizontalnih redova	3
Ukupan broj 18 mm modula	36
Tip prednje ploče	Puna i ploče sa otvorima
Broj otvora	3 izreza
Visina	355 mm
Širina	255 mm
Dubina	110 mm

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,500 cm
Package 1 Width	29,000 cm
Package 1 Length	41,500 cm
Package 1 Weight	1,721 kg
Unit Type of Package 2	S04
Number of Units in Package 2	6
Package 2 Height	30,000 cm
Package 2 Width	40,000 cm
Package 2 Length	60,000 cm

Package 2 Weight	10,976 kg
Unit Type of Package 3	P12
Number of Units in Package 3	24
Package 3 Height	45,000 cm
Package 3 Width	80,000 cm
Package 3 Length	120,000 cm
Package 3 Weight	55,904 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------