

Tehničke karakteristike proizvoda Karakteristike

NSYVDM16U4P zidni rek VDM 16U zakretna šasija D400



Pregled

Prezentacija	NEMA 12/IP66 rated assembled enclosure for OT, IT and networking applications. Form factor to easily install on the wall. Configurable to work as a ventilated enclosure with the addition of IP54 Climasys ventilation components. Ventilation system not included
Vreme isporuke	Usually Ships within 4 Weeks

Osnovne informacije

Grupa proizvoda	Spacial
Ime proizvoda	Spacial VDM
Application	Elektronska aplikacija
Tip proizvoda ili komponente	Kompaktni orman
Tip kućišta	1-kućište
Tip reka	Zakretni
Nazivna visina ormana	800 mm
Nazivna širina ormana	600 mm
Nazivna dubina ormana	250 mm
Tip dodatnog instalacionog pribora	Montaža na zid
Namena proizvoda	Elektronske komponente i mreže
Sastav uređaja	1 ploča za kablovske uvodnice: dno 2 brava: 19" zakretni rek 1 telo 1 vrata sa bravom 1 19" zakretni rek

Dopunske informacije

Tip vrata	Providna
Broj vrata	Prednji deo: 1 vrata
Otvaranje vrata	Reverzibilno (120 °)
Tip zaključavanja	Zaključavanje u 3 tačke, 3 mm dvostruki prorez
Tip uvodne ploče	Standardna
Broj 19" jedinica	16
Dostupnost za operacije	Prednji deo
Odvojni delovi	Vrata sa šarkama Rek sa elementom za fiksiranje
Materijal	Orman i 19" rek: čelik
Obrada površine	Orman i 19" rek: epoksi poliester prah
Boja	Orman i 19" rek: siva (RAL 7035)
Standardi	IEC 62208
Masa proizvoda	34,5 kg
Širina	600 mm

Visina	800 mm
Dubina	250 mm

Okruženje

Ip stepen zaštite	IP66 u skladu sa IEC 60529
Ik stepen zaštite	IK08 u skladu sa IEC 62262

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	95,0 cm
Package 1 Width	120,0 cm
Package 1 Length	80,0 cm
Package 1 Weight	59,0 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda

Ugovorna garancija

Garancija	18 meseci
-----------	-----------