

Tehničke karakteristike proizvoda

Karakteristike

NU044218

Ram dekorativni 1 element IP44 beli



Osnovne informacije

| | |
|------------------------------|-----------------|
| Grupa proizvoda | New Unica |
| Primena uređaja | Montaža |
| Tip proizvoda ili komponente | Dekoratívni ram |
| Ime dekorativnog elementa | Unica System+ |
| Broj dvostrukih modula | Jednostruki |
| Pravac instalacije | Horizontalno |
| Tip prekidača | Pojedinačno |
| Broj modula | 2 modula |
| Način pričvršćivanja | Zavrtnjima |
| Nijansa boje | Bela (RAL 9003) |

Dopunske informacije

| | |
|---------------------------------|--|
| Zaštitna oprema | Montažni ram |
| Materijal | Termoplastika ABS-UV stabilizovana: dekorativni ram |
| Završna obrada | Sjajno |
| Standardi | IEC 60884-1 IEC 60669-1 |
| Širina | 80 mm |
| Visina | 90 mm |
| Dubina | 30 mm |
| Masa proizvoda | 0,052 kg |
| Otpornost na hemijske supstance | Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan |

Okruženje

| | |
|-------------------|------|
| Ik stepen zaštite | IK04 |
| Ip stepen zaštite | IP44 |

Pakovanje

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4,000 cm |
| Package 1 Width | 10,500 cm |
| Package 1 Length | 15,000 cm |
| Package 1 Weight | 54,000 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |

| | |
|------------------------------|-----------|
| Package 2 Height | 12,500 cm |
| Package 2 Width | 12,500 cm |
| Package 2 Length | 18,500 cm |
| Package 2 Weight | 333,000 g |
| Unit Type of Package 3 | S04 |
| Number of Units in Package 3 | 90 |
| Package 3 Height | 30,000 cm |
| Package 3 Width | 40,000 cm |
| Package 3 Length | 60,000 cm |
| Package 3 Weight | 6,770 kg |

Održivost ponude

| | |
|------------------------------|--|
| Status održive ponude | Green Premium proizvod |
| Propis REACH | REACH Deklaracija |
| REACH bez SVHC | Da |
| EU RoHS direktiva | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija |
| Bez toksičnih teških metala | Da |
| Bez žive | Da |
| RoHS regulativa za Kinu | RoHS Deklaracija Za Kinu |
| Informacije o RoHS izuzecima | Da |
| Izjava o zaštiti okoliša | Profil Ekološke Prihvatljivosti Proizvoda |
| Profil cirkularnosti | Nema potrebe za namenskim operacijama recikliranja |