

Tehničke karakteristike proizvoda

Karakteristike

NU200854

Ram dek. Unica Studio 4 elemen. antracit



Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekorativni ram
Ime dekorativnog elementa	Unica Studio
Broj dvostrukih modula	Četvorostruki
Pravac instalacije	Horizontalno vertikalno
Tip prekidača	Quadruple
Broj modula	4 x 2 modules
Način pričvršćivanja	Utično
Nijansa boje	Antracit (RAL 7021)

Dopunske informacije

Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram
Završna obrada	Sjajno
Standardi	IEC 60669-1 IEC 60884-1
Širina	298 mm
Visina	85 mm
Dubina	10 mm
Masa proizvoda	0,042 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP21 D

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1 cm
Package 1 Width	8,5 cm
Package 1 Length	30 cm
Package 1 Weight	46 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7,4 cm

Package 2 Width	9,5 cm
Package 2 Length	32 cm
Package 2 Weight	301 g
Unit Type of Package 3	S04
Number of Units in Package 3	100
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	6,626 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja