

Tehničke karakteristike proizvoda

Karakteristike

NU270356M

Ram dekorativni 3M beli alumin./crni



Osnovne informacije

| | |
|------------------------------|--------------------|
| Grupa proizvoda | New Unica |
| Primena uređaja | Montaža |
| Tip proizvoda ili komponente | Dekoratívni ram |
| Ime dekorativnog elementa | Unica Studio Metal |
| Broj dvostrukih modula | Jednostruki |
| Pravac instalacije | Horizontalno |
| Tip prekidača | Pojedinačno |
| Broj modula | 3 modula |
| Način pričvršćivanja | Zavrtnjima |
| Nijansa boje | White aluminium |
| Side color | Crno (RAL 7021) |

Dopunske informacije

| | |
|---------------------------------|--|
| Materijal | Polikarbonat: međuploča |
| Završna obrada | Brušena završna obrada |
| Količina po setu | Set od 10 |
| Standardi | IEC 60669-1 IEC 60884-1 |
| Širina | 120 mm |
| Visina | 85 mm |
| Dubina | 10 mm |
| Masa proizvoda | 0,027 kg |
| Otpornost na hemijske supstance | Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan |

Okruženje

| | |
|-------------------|--------|
| Ik stepen zaštite | IK04 |
| Ip stepen zaštite | IP21 D |

Pakovanje

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1,1 cm |
| Package 1 Width | 8,5 cm |
| Package 1 Length | 12,0 cm |
| Package 1 Weight | 22,0 g |
| Unit Type of Package 2 | BB1 |

| | |
|------------------------------|----------|
| Number of Units in Package 2 | 10 |
| Package 2 Height | 13,0 cm |
| Package 2 Width | 12,3 cm |
| Package 2 Length | 18,5 cm |
| Package 2 Weight | 322,2 g |
| Unit Type of Package 3 | S04 |
| Number of Units in Package 3 | 180 |
| Package 3 Height | 30,0 cm |
| Package 3 Width | 40,0 cm |
| Package 3 Length | 60,0 cm |
| Package 3 Weight | 6,503 kg |

Održivost ponude

| | |
|------------------------------|--|
| Status održive ponude | Green Premium proizvod |
| Propis REACh | REACh Deklaracija |
| REACh bez SVHC | Da |
| EU RoHS direktiva | Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS) EU RoHS deklaracija |
| Bez toksičnih teških metala | Da |
| Bez žive | Da |
| RoHS regulativa za Kinu | RoHS Deklaracija Za Kinu |
| Informacije o RoHS izuzecima | Da |
| Izjava o zaštiti okoliša | Profil Ekološke Prihvatljivosti Proizvoda |
| Profil cirkularnosti | Nema potrebe za namenskim operacijama recikliranja |