

# Tehničke karakteristike proizvoda

## Karakteristike

# NU301954

## USB punjač dvostruki tip A+C 18W



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	USB punjač
Prezentacija uređaja	Mehanizam
Uslovi upotrebe	U zatvorenom

### Dopunske informacije

Primena uređaja	Punjač
Montaža uređaja	Ugradno
Broj modula	2 modula
Type of USB power supply	USB type A + C
Nijansa boje	Antracit (RAL 7021)
Završna obrada	Painted powder coated
[ue] nazivni napon	100...240 V AC 50/60 Hz
Maksimalna potrošnja u w	0,1 W
Nazivna izlazna snaga	18 W
Servisni vek u satima	30000 sati 18 W
Broj utičnica	2
Integrirani načini povezivanja	1 USB tip A 5 V DC, maksimalna struja opterećenja: 1 A 1 USB type C 5 V DC, maksimalna struja opterećenja: 2.4 A
Materijal	Plastika: kućište
Tip zaštite	Kratki spoj Preskok Pregrevanje Prenaponska Prekostrujna
Broj priključaka	2 vijčani priključci
Oblik glave zavrtnja	Pozidriv No 1
Kapacitet priključaka	2 x 0.75...2 x 2.5 mm <sup>2</sup> za kruti kabl(ovi) 2 x 0.75...2 x 2.5 mm <sup>2</sup> za fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	7 mm
Način pričvršćivanja	Utično
Temperatura okoline za rad uređaja	0...40 °C
Visina	45 mm
Širina	45 mm
Dubina	40 mm

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu primenu. Dužnost je korisnika odnosno integratora da izvrši, primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovde navedenih informacija.

Dubina za ugradnju	32 mm
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

## Okruženje

Električna klasa izolacije	Klasa II
Ik stepen zaštite	IK04
Ip stepen zaštite	IP20

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7,700 cm
Package 1 Width	9,500 cm
Package 1 Length	9,500 cm
Package 1 Weight	113,000 g
Unit Type of Package 2	S02
Number of Units in Package 2	9
Package 2 Height	15,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	1,243 kg
Unit Type of Package 3	P06
Number of Units in Package 3	144
Package 3 Height	77,000 cm
Package 3 Width	80,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	24,272 kg

## Održivost ponude

EU RoHS direktiva	Na ispitivanju
Sustainable packaging	Yes