

Tehničke karakteristike proizvoda Karakteristike

NU320744 Taster prekidač za roletne 6A 2M



Osnovne informacije

Range of product	New Unica
Tip proizvoda ili komponente	Taster za roletne
Prezentacija uređaja	Mehanizam sa centralnom pločom
Vrsta tehnologije	Elektromehanička
Funkcija prekidača	Za roletne
Broj prekidača	2
Primena uređaja	Upravljanje
Primena prekidača	Roletne
Nijansa boje	Bež (RAL 1013)
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Nazivna struja	6 A
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Električna trajnost	20000 ciklusa, $\cos \phi = 0,6$
Otpornost izolacije	> 5 MOhm pri 500 V
Dielektrična snaga	2000 V
Minimalna moć isključenja opterećenja	200 operacija $1.25 I_n$ i $1.1 U_n$, $\cos \phi = 0,3$
Uslovi upotrebe	U zatvorenom
Udaljenost otvaranja	> 3 mm
Izvršni organ	Preklopni prekidač
Broj modula	2 modula
Signalna lampica	Bez LED
Povezivanje - priključci	Priključci bez zavrtnjeva
Poprečni presek kabla	0...2,5 mm ² kruti kabl 0...2,5 mm ² fleksibilni kabl
Materijal	CuZn15: priključci Termoplastika ABS-UV stabilizovana: mechanism rocker PC (polikarbonat) GF10 FR: kućište PBT (polibutilen-tereftalat) GF30: release button
Označavanje	Strelica
Završna obrada	Sjajno
Specific treatment - integrated within the material	Neobrađeno
Montaža uređaja	Ugradno
Način pričvršćivanja	Utično
Širina	45 mm
Visina	45 mm
Dubina	44,35 mm
Dubina za ugradnju	32,8 mm
Masa proizvoda	0,0331 kg
Temperatura okoline za rad uređaja	-5...40 °C
Temperatura okoline za skladištenje	-5...50 °C

Standardi	EN 60669-1 LV direktiva EMC direktiva
Sertifikacija proizvoda	CE[RETURN]Aenor[RETURN]EAC[RETURN]NF
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ip stepen zaštite	IP4X
Ik stepen zaštite	IK04
Karakteristike životne sredine	Ulje UV otpornost Aceton Tečni sapun Tečnost za čišćenje prozora Benzin Alkohol Izbeljivač

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,6 cm
Package 1 Width	4,5 cm
Package 1 Length	4,5 cm
Package 1 Weight	33,0 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15,0 cm
Package 2 Width	30,0 cm
Package 2 Length	40,0 cm
Package 2 Weight	975,0 g
Unit Type of Package 3	P06
Number of Units in Package 3	320
Package 3 Height	77,0 cm
Package 3 Width	80,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	24,1 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja