

Tehničke karakteristike proizvoda Karakteristike

NU321154 Prekidač serijski 10A 2M



Osnovne informacije

Range of product	New Unica
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam sa centralnom pločom
Vrsta tehnologije	Elektromehanička
Funkcija prekidača	Jednopolni izborni
Broj prekidača	2
Primena uređaja	Kontrola svetlosti
Zaštitna oprema	Konektor internog napajanja
Nijansa boje	Antracit (RAL 7021)
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Nazivna struja	10 AX
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Električna trajnost	20000 ciklusa, $\cos \phi = 0,6$
Otpornost izolacije	> 5 MOhm pri 500 V
Dielektrična snaga	2000 V
Minimalna moć isključenja opterećenja	200 operacija $1.25 I_n$ i $1.1 U_n$, $\cos \phi = 0,3$
Uslovi upotrebe	U zatvorenom
Udaljenost otvaranja	> 3 mm
Izvršni organ	Preklopni prekidač
Broj modula	2 modula
Povezivanje - priključci	Priključci bez zavrtnjeva
Poprečni presek kabl	0...2,5 Mm ² kruti kabl 0...2,5 mm ² fleksibilni kabl
Materijal	PBT (polybutylene terephthalate) GF31: release button CuZn15: internal link Termoplastika ABS-UV stabilizovana: mechanism rocker PC (polikarbonat) GF10 FR: kućište CuZn37: priključci
Označavanje	Bez oznake
Završna obrada	Mat
Specific treatment - integrated within the material	Slikano
Način pričvršćivanja	Utično
Širina	45 mm
Visina	45 mm
Dubina	34,25 mm
Dubina za ugradnju	21,15 mm
Masa proizvoda	0,0284 kg
Temperatura okoline za rad uređaja	-5...40 °C
Temperatura okoline za skladištenje	-5...50 °C
Standardi	EN 60669-1 LV direktiva EMC direktiva

Sertifikacija proizvoda	CE[RETURN]Aenor[RETURN]EAC[RETURN]NF
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ip stepen zaštite	IP4X
Ik stepen zaštite	IK04
Karakteristike životne sredine	Alkohol Tečnost za čišćenje prozora Aceton Benzin UV otpornost Ulje Izbeljivač Tečni sapun

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,0 cm
Package 1 Width	4,5 cm
Package 1 Length	4,5 cm
Package 1 Weight	30,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,5 cm
Package 2 Width	14,0 cm
Package 2 Length	26,0 cm
Package 2 Weight	373,0 g
Unit Type of Package 3	S04
Number of Units in Package 3	240
Package 3 Height	30,0 cm
Package 3 Width	40,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	9,583 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja