

# Tehničke karakteristike proizvoda

## Karakteristike

# NU341418

## Utičnica RJ45 CAT6 UTP 1 modul bela



### Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	Komunikacione utičnice
Primena uređaja	Komunikacija
Prezentacija uređaja	Mehanizam
Nijansa boje	Bela (RAL 9003)
Tip komunikacione utičnice	RJ45 8 kontakt(i) kat.6 < 250 MHz
Zaštitna oprema	Zaštitni poklopac Nosac oznake

### Dopunske informacije

Tip komunikacione mreže	1000BASE-TX
Protokol komunikacionog porta	ATM 1200 Mbps
Broj modula	1 modul
Broj utičnica	1
Tip dizajna	Infraplus
Tip priključka	S-One
Tip oklopa kabla	U/UTP
Način formiranja kabla	Neoklopljen kabl sa upredenim paricama
Povezivanje - priključci	Na klik
Montaža uređaja	Ugradno
Način fiksiranja	Utično
Pravac instalacije	Ravno
Materijal	Termoplastika ABS-UV stabilizovana: centralna pločica
Količina po setu	1
Dubina	40,5 mm
Širina	22,5 mm
Visina	45 mm
Dubina za ugradnju	40,5 mm
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

### Okruženje

Ip stepen zaštite	IP20
Ik stepen zaštite	IK01
Temperatura okoline za rad	-25...55 °C
Temperatura okoline za skladištenje	-5...35 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,7 cm
Package 1 Width	2,2 cm
Package 1 Length	4,5 cm
Package 1 Weight	17,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5,5 cm
Package 2 Width	14,0 cm
Package 2 Length	26,0 cm
Package 2 Weight	180,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	1,05 kg

## Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	<a href="#">REACH Deklaracija</a>
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno <a href="#">EU RoHS Deklaracija</a>
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	<a href="#">RoHS Deklaracija Za Kinu</a>
Informacije o RoHS izuzecima	<a href="#">Da</a>
Izjava o zaštiti okoliša	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.