

Tehničke karakteristike proizvoda

Karakteristike

NU341718

Utičnica RJ45 CAT6 STP 2 modula bela



Osnovne informacije

| | |
|------------------------------|-----------------------------------|
| Grupa proizvoda | New Unica |
| Tip proizvoda ili komponente | Komunikacione utičnice |
| Primena uređaja | Komunikacija |
| Prezentacija uređaja | Mehanizam |
| Nijansa boje | Bela (RAL 9003) |
| Tip komunikacione utičnice | RJ45 8 kontakt(i) kat.6 < 250 MHz |
| Zaštitna oprema | Zaštitni poklopac Nosac oznake |

Dopunske informacije

| | |
|---------------------------------|--|
| Tip komunikacione mreže | 1000BASE-TX |
| Protokol komunikacionog porta | ATM 1200 Mbps |
| Broj modula | 2 modula |
| Broj utičnica | 1 |
| Tip dizajna | Infraplus |
| Tip priključka | S-One |
| Tip oklopa kabla | STP |
| Način formiranja kabla | Oklopljen kabl sa upredenim paricama |
| Povezivanje - priključci | Na klik |
| Montaža uređaja | Ugradno |
| Način fiksiranja | Utično |
| Pravac instalacije | Ravno |
| Materijal | Termoplastika ABS-UV stabilizovana: centralna pločica |
| Dubina | 40,5 mm |
| Širina | 45 mm |
| Visina | 45 mm |
| Dubina za ugradnju | 40,5 mm |
| Otpornost na hemijske supstance | Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan |

Okruženje

| | |
|-------------------------------------|-------------|
| Ip stepen zaštite | IP20 |
| Ik stepen zaštite | IK01 |
| Temperatura okoline za rad | -25...55 °C |
| Temperatura okoline za skladištenje | -25...55 °C |

Pakovanje

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4,1 cm |
| Package 1 Width | 4,5 cm |
| Package 1 Length | 4,5 cm |
| Package 1 Weight | 45,0 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 6,0 cm |
| Package 2 Width | 14,0 cm |
| Package 2 Length | 26,0 cm |
| Package 2 Weight | 524,0 g |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 100 |
| Package 3 Height | 30,0 cm |
| Package 3 Width | 30,0 cm |
| Package 3 Length | 40,0 cm |
| Package 3 Weight | 5,693 kg |

Održivost ponude

| | |
|------------------------------|---|
| Status održive ponude | Green Premium proizvod |
| Propis REACH | REACH Deklaracija |
| REACH bez SVHC | Da |
| EU RoHS direktiva | Usaglašeno EU RoHS Deklaracija |
| Bez toksičnih teških metala | Da |
| Bez žive | Da |
| Sustainable packaging | Yes |
| RoHS regulativa za Kinu | RoHS Deklaracija Za Kinu |
| Informacije o RoHS izuzecima | Da |
| Izjava o zaštiti okoliša | Profil Ekološke Prihvatljivosti Proizvoda |
| Profil cirkularnosti | Nema potrebe za namenskim operacijama recikliranja |
| WEEE | Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke. |