

Tehničke karakteristike proizvoda

Karakteristike

NU341830

2 USB 2.0 utičnica napajanja 2m alu



Osnovne informacije

Grupa proizvoda	New Unica
Tip proizvoda ili komponente	USB punjač
Prezentacija uređaja	Mehanizam

Dopunske informacije

Primena uređaja	Punjač
Montaža uređaja	Ugradno
Broj modula	2 modula
Type of USB power supply	USB type A + A
Nijansa boje	Aluminijum
[ue] nazivni napon	100...240 V AC 50/60 Hz
Nazivna izlazna snaga	10,5 W
Broj utičnica	2
Integrirani načini povezivanja	2 USB tip A 5 V DC, maksimalna struja opterećenja: 2.1 A
Materijal	PC (polikarbonat) GF10 FR: kućište PC (polikarbonat) GF10 FR: unutrašnji poklopac Termoplastika ABS-UV stabilizovana: centralna pločica
Tip zaštite	Zaštita od kratkog spoja
Broj priključaka	2 vijčani priključci
Oblik glave zavrtnja	Pozidriv No 1
Kapacitet priključaka	1.5...2.5 mm ² za kruti kabl(ovi) 1.5...2.5 mm ² za fleksibilni kabl(ovi)
Dužina ogoljenog dela žice	8 mm
Kompatibilnost proizvoda	Svi uređaji koji ispunjavaju EN 62684 standard
Način pričvršćivanja	Utično
Tip pakovanja	Pakovanje u kesicama
Temperatura okoline za rad uređaja	5...45 °C
Temperatura okoline za skladištenje	-5...50 °C
Standardi	IEC 62368-1 EN 61000-6-3 EN 61000-6-1 IEC 62680-3
Visina	45 mm
Širina	45 mm
Dubina	40 mm
Dubina za ugradnju	27 mm

Masa proizvoda	0,082 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Električna klasa izolacije	Klasa II
Ik stepen zaštite	IK04
Ip stepen zaštite	IP2XC

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,0 cm
Package 1 Width	4,8 cm
Package 1 Length	4,8 cm
Package 1 Weight	52,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6,0 cm
Package 2 Width	14,2 cm
Package 2 Length	26,5 cm
Package 2 Weight	592,0 g
Unit Type of Package 3	S02
Number of Units in Package 3	50
Package 3 Height	15,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	3,264 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	Da
Izjava o zaštiti okoliša	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Informacije O Kraju Radnog Veka
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.