



## Tehničke karakteristike proizvoda Karakteristike

# PKE32M7C4

Mureva Wander utikač - ravni - 32 A - 3P + E -  
380...440 V AC - IP67

### Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utikač
Kratko ime uređaja	Mureva plug
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + E
Tip mreže	AC
Standard utičnice	Industrijski

### Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	32 A
[ue] nazivni napon	380...440 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	3 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	2,5...6 mm <sup>2</sup>
Kablovski uvod	Vodilica Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,22 kg
Visina	95 mm
Širina	95 mm
Dubina	152 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

### Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,000 cm
Package 1 Width	9,000 cm
Package 1 Length	16,000 cm
Package 1 Weight	264,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	21,000 cm
Package 2 Width	27,000 cm
Package 2 Length	27,000 cm
Package 2 Weight	1,765 kg
Unit Type of Package 3	S03
Number of Units in Package 3	12
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	3,970 kg

## Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	661ec80b-b956-4b0a-92bb-53046f4cfb4c
Uredba REACh	<a href="#">REACH Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	17

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------