

# Tehničke karakteristike proizvoda

## Karakteristike

# PKF16F423

Mureva utičnica - vijčana - pod uglom - 16A -  
2P + E - 200...250 V AC - panel

### Osnovne informacije

|                                   |               |
|-----------------------------------|---------------|
| Grupa proizvoda                   | Mureva        |
| Tip proizvoda ili komponente      | Utičnica      |
| Kratko ime uređaja                | Mureva socket |
| Kategorija priključnice i utikača | Niskonaponska |
| Broj polova                       | 2P + E        |
| Tip mreže                         | AC            |
| Standard utičnice                 | Industrijski  |

### Dopunske informacije

|   |   |
|---|---|
| Način montiranja                                      | Montaža na panel                        |
| Kategorija priključnice i utikača                     | Pod uglom                               |
| [in] nazivna struja                                   | 16 A                                    |
| [ue] nazivni napon                                    | 200...250 V                             |
| Mrežna frekvencija                                    | 50/60 Hz                                |
| Pozicija kontakta uzemljenja u smeru kazaljke na satu | 6 h                                     |
| Materijal utikača, utičnice                           | Kućište: samogasivi konstruisan polimer |
| Materijal kontakta                                    | Priključci: mesing                      |
| Povezivanje - priključci                              | Neodvojivi zavrtnji                     |
| Poprečni presek kabla                                 | 1...4 mm <sup>2</sup>                   |
| Masa proizvoda  | 0,136 kg                                |
| Dimenzija baze  | 65 x 85 mm                              |
| Visina  | 85 mm                                   |
| Širina  | 65 mm                                   |
| Dubina  | 103 mm                                  |
| Boja  | Siva (RAL 7035)                         |
| Boja poklopca   | Plava                                   |

### Okruženje

|                            |  |
|----------------------------|--|
| Standardi                  | IEC 60309-2<br>IEC 60309-1                         |
| Ip stepen zaštite          | IP44 conforming to IEC 60529                       |
| Ik stepen zaštite          | IK08 conforming to EN 62262                        |
| Otpornost na vatru         | 850 °C u skladu sa IEC 60695-2-1                   |
| Relativna vlažnost         | 50 % pri 40 °C<br>70 % pri 30 °C<br>90 % pri 20 °C |
| Temperatura okoline za rad | 35 °C 86400 s )                                    |

## Pakovanje

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 7,000 cm  |
| Package 1 Width              | 6,500 cm  |
| Package 1 Length             | 8,500 cm  |
| Package 1 Weight             | 117,000 g |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 12,400 cm |
| Package 2 Width              | 26,000 cm |
| Package 2 Length             | 27,000 cm |
| Package 2 Weight             | 1,320 kg  |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 30        |
| Package 3 Height             | 30,000 cm |
| Package 3 Width              | 30,000 cm |
| Package 3 Length             | 40,000 cm |
| Package 3 Weight             | 4,500 kg  |

## Održivost ponude

|                                    |   |
|------------------------------------|---|
| Pakovanje bez plastike             | Da  |
| Pakovanje sa recikliranim kartonom | Da  |
| SCIP broj                          | 89350e0d-a4ac-4516-bf86-fdaed8a227fc                      |
| Uredba REACh                       | <a href="#">REACH Deklaracija</a>                         |
| EU RoHS direktiva                  | Usaglašeno sa izuzecima                                   |
| Bez žive                           | Da  |
| Informacije o izuzeću od RoHS      | <a href="#">Da</a>  |
| Kina RoHS regulacija               | <a href="#">RoHS Deklaracija Za Kinu</a>                  |
| Izjava o zaštiti okoline           | <a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a> |
| Profil cirkularnosti               | Nema potrebe za namenskim operacijama recikliranja        |
| Povraćaj                           | No  |
| Emisija ugljenika (kg CO2 eq.)     | 5   |

## Ugovorna garancija

|           |           |
|-----------|-----------|
| Garancija | 18 meseci |
|-----------|-----------|