



# Tehničke karakteristike proizvoda

## Karakteristike

# PKF16M423

Mureva Wander utičnica - ravna - 16 A - 2P + E  
- 200...250 V AC - IP44

### Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	2P + E
Tip mreže	AC
Standard utičnice	Industrijski

### Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	200...250 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	1...4 mm <sup>2</sup>
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Vodilica Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,16 kg
Visina	78 mm
Širina	78 mm
Dubina	140 mm
Boja	Siva (RAL 7035)
Boja poklopca	Plava

### Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP44 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,000 cm
Package 1 Width	7,500 cm
Package 1 Length	14,700 cm
Package 1 Weight	148,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12,200 cm
Package 2 Width	26,400 cm
Package 2 Length	27,200 cm
Package 2 Weight	1,588 kg
Unit Type of Package 3	S03
Number of Units in Package 3	30
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	5,251 kg

## Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	6

## Ugovorna garancija

Garancija	18 months
-----------	-----------