



Tehničke karakteristike proizvoda

Karakteristike

PKF16M435

Mureva Wander utičnica - ravna - 16 A - 3P +
N + E - 380...415 V AC - IP44

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	1...4 mm ²
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Vodilica Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,21 kg
Visina	97 mm
Širina	97 mm
Dubina	153 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP44 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6,500 cm
Package 1 Width	9,500 cm
Package 1 Length	16,500 cm
Package 1 Weight	205,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17,000 cm
Package 2 Width	27,000 cm
Package 2 Length	27,000 cm
Package 2 Weight	2,206 kg
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	4,800 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACh	REACh Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	8

Ugovorna garancija

Garancija	18 meseci
-----------	-----------