



Tehničke karakteristike proizvoda

Karakteristike

PKF16M723

Mureva Wander utičnica - ravna - 16 A - 2P + E
- 200...250 V AC - IP67

Osnovne informacije

| | |
|-----------------------------------|-----------------|
| Grupa proizvoda | Mureva |
| Tip proizvoda ili komponente | Wander utičnica |
| Kratko ime uređaja | Mureva screw |
| Kategorija priključnice i utikača | Niskonaponska |
| Broj polova | 2P + E |
| Tip mreže | AC |
| Standard utičnice | Industrijski |

Dopunske informacije

| | |
|---|---|
| Kategorija priključnice i utikača | Ravna |
| [in] nazivna struja | 16 A |
| [ue] nazivni napon | 200...250 V |
| Mrežna frekvencija | 50/60 Hz |
| Pozicija kontakta uzemljenja u smeru kazaljke na satu | 6 h |
| Materijal utikača, utičnice | Kućište: samogasivi konstruisan polimer |
| Materijal kontakta | Priključci: mesing |
| Povezivanje - priključci | Neodvojivi zavrtnji |
| Poprečni presek kabla | 1...4 mm ² |
| Spoljašnji prečnik kabla | 8...15 mm |
| Kablovski uvod | Kablovska uvodnica |
| Tip navoja | Pg 21 |
| Masa proizvoda | 0,17 kg |
| Visina | 84 mm |
| Širina | 84 mm |
| Dubina | 142 mm |
| Boja | Siva (RAL 7035) |
| Boja poklopca | Plava |

Okruženje

| | |
|----------------------------|--|
| Standardi | IEC 60309-2 IEC 60309-1 |
| Ip stepen zaštite | IP67 conforming to IEC 60529 |
| Ik stepen zaštite | IK08 conforming to EN 62262 |
| Otpornost na vatru | 850 °C u skladu sa IEC 60695-2-1 |
| Relativna vlažnost | 50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C |
| Temperatura okoline za rad | 35 °C 86400 s) -25...40 °C |

Pakovanje

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7,0 cm |
| Package 1 Width | 8,0 cm |
| Package 1 Length | 15,0 cm |
| Package 1 Weight | 174,0 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Height | 12,4 cm |
| Package 2 Width | 26,4 cm |
| Package 2 Length | 27,0 cm |
| Package 2 Weight | 1,866 kg |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 30 |
| Package 3 Height | 30,0 cm |
| Package 3 Width | 30,0 cm |
| Package 3 Length | 40,0 cm |
| Package 3 Weight | 6,085 kg |

Održivost ponude

| | |
|------------------------------------|---|
| Pakovanje bez plastike | Da |
| Pakovanje sa recikliranim kartonom | Da |
| SCIP broj | 89350e0d-a4ac-4516-bf86-fdaed8a227fc |
| Uredba REACh | REACH Deklaracija |
| EU RoHS direktiva | Usaglašeno sa izuzecima |
| Bez žive | Da |
| Informacije o izuzeću od RoHS | Da |
| Kina RoHS regulacija | RoHS Deklaracija Za Kinu |
| Izjava o zaštiti okoline | Profil Ekološke Prihvatljivosti Proizvoda |
| Profil cirkularnosti | Nema potrebe za namenskim operacijama recikliranja |
| Povraćaj | No |
| Emisija ugljenika (kg CO2 eq.) | 6 |

Ugovorna garancija

| | |
|-----------|-----------|
| Garancija | 18 meseci |
|-----------|-----------|