



## Tehničke karakteristike proizvoda Karakteristike

## PKF16M734

Mureva Wander utičnica - ravna - 16 A - 3P + E  
- 380...415 V AC - IP67

### Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Wander utičnica
Kratko ime uređaja	Mureva screw
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + E
Tip mreže	AC
Standard utičnice	Industrijski

### Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	1...4 mm <sup>2</sup>
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,2 kg
Visina	87 mm
Širina	87 mm
Dubina	152 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

### Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,5 cm
Package 1 Width	9,0 cm
Package 1 Length	16,0 cm
Package 1 Weight	196,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	18,2 cm
Package 2 Width	26,4 cm
Package 2 Length	26,8 cm
Package 2 Weight	2,148 kg
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	4,783 kg

## Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Izjava o zaštiti okoline	<a href="#">Profil Ekološke Prihvatljivosti Proizvoda</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	8

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------