



Tehničke karakteristike proizvoda

Karakteristike

PKF32F735

Mureva utičnica - vijčana - pod uglom - 32A -
3P + N + E - 380...415 V AC-panel

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

Dopunske informacije

Način montiranja	Montaža na panel
Kategorija priključnice i utikača	Pod uglom
[in] nazivna struja	32 A
[ue] nazivni napon	380...415 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	6 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Neodvojivi zavrtnji
Poprečni presek kabla	2,5...10 mm ²
Masa proizvoda	0,26 kg
Dimenzija baze	90 x 100 mm
Visina	100 mm
Širina	102 mm
Dubina	121 mm
Boja	Siva (RAL 7035)
Boja poklopca	Crvena

Okruženje

Standardi	IEC 60309-2 IEC 60309-1
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-1
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s)

Informacije navedene u ovoj dokumentaciji predstavljaju opšti opis odnosno tehničke karakteristike performansi proizvoda. Dokumentacija nije namenjena da bude zamena za niti se može koristiti za određivanje prikladnosti i pouzdanosti proizvoda za specifičnu krajnju primenu. Dužnost je korisnika odnosno integratora da izvrši primerenu i sveobuhvatnu analizu rizika, procenu i proveru proizvoda u pogledu odgovarajuće specifične primene ili načina korišćenja. Ni Schneider Electric Industries SAS ni njegova povezana ili zavisna društva neće snositi odgovornost za zloupotrebu ovdenavedenih informacija.

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9,500 cm
Package 1 Width	10,000 cm
Package 1 Length	10,500 cm
Package 1 Weight	267,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	7
Package 2 Height	17,000 cm
Package 2 Width	27,000 cm
Package 2 Length	27,000 cm
Package 2 Weight	2,029 kg
Unit Type of Package 3	S03
Number of Units in Package 3	14
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	4,457 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACH	REACH Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	22

Ugovorna garancija

Garancija	18 meseci
-----------	-----------