



Tehničke karakteristike proizvoda

Karakteristike

PKS62G

Mureva utičnica - siva - 2P + E - 10/16 A - 250 V - šuko - IP54 - ugradna-bočna

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Utičnica
Kratko ime uređaja	Mureva socket
Kategorija priključnice i utikača	Niskonaponska
Broj polova	2P + E
Tip mreže	AC
Standard utičnice	Nemački

Dopunske informacije

[in] nazivna struja	10 A 16 A
Mrežna frekvencija	50/60 Hz
[ue] nazivni napon	250 V
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Pinovi: nerđajući čelik Opruge: nerđajući čelik
Tip poklopca	Poklopac
Montaža uređaja	Ugradno
Način montiranja	Montaža na panel
Povezivanje - priključci	Neodvojivi zavrtnji
Položaj ulaza provodnika	Strana
Masa proizvoda	0,05 kg
Dimenzija baze	65 x 85 mm
Visina	85 mm
Širina	65 mm
Dubina	45,2 mm
Boja	Siva (RAL 7035)

Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP54 conforming to IEC 60529
Ik stepen zaštite	IK09 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Temperatura okoline za rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	6,500 cm
Package 1 Length	8,500 cm
Package 1 Weight	56,700 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	14,000 cm
Package 2 Width	19,000 cm
Package 2 Length	28,500 cm
Package 2 Weight	1,219 kg
Unit Type of Package 3	S03
Number of Units in Package 3	60
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	4,075 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Ne
SCIP broj	52b60409-d705-46c7-9ba3-cc3ef6e307da
Uredba REACh	REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
Povraćaj	No

Ugovorna garancija

Garancija	18 meseci
-----------	-----------