



# Tehničke karakteristike proizvoda Karakteristike

## PKX16M715

Mureva wander plug - straight - 16 A - 3P + N +  
E - 100...130 V AC - IP67

### Osnovne informacije

Grupa proizvoda	PratiKa
Tip proizvoda ili komponente	Wander utikač
Kratko ime uređaja	PratiKa utičnica
Kategorija priključnice i utikača	Niskonaponska
Broj polova	3P + N + E
Tip mreže	AC
Standard utičnice	Industrijski

### Dopunske informacije

Kategorija priključnice i utikača	Ravna
[in] nazivna struja	16 A
[ue] nazivni napon	100...130 V
Mrežna frekvencija	50/60 Hz
Pozicija kontakta uzemljenja u smeru kazaljke na satu	4 h
Materijal utikača, utičnice	Kućište: samogasivi konstruisan polimer
Materijal kontakta	Priključci: mesing
Povezivanje - priključci	Brzo povezivanje
Poprečni presek kabla	1...2,5 mm <sup>2</sup>
Spoljašnji prečnik kabla	8...15 mm
Kablovski uvod	Vodilica Kablovska uvodnica
Tip navoja	Pg 21
Masa proizvoda	0,245 kg
Visina	142 mm
Širina	89 mm
Dubina	89 mm
Boja	Siva (RAL 7035)
Boja poklopca	Žuta

### Okruženje

Standardi	IEC 60309-2 IEC 60309-1
Ip stepen zaštite	IP67 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11
Relativna vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska visina za rad	2000 m
Temperatura okoline za rad	35 °C 86400 s ) -25...40 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10,0 cm
Package 1 Width	9,0 cm
Package 1 Length	7,0 cm
Package 1 Weight	180,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	17,0 cm
Package 2 Width	27,0 cm
Package 2 Length	26,3 cm
Package 2 Weight	2,5 kg
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	5,487 kg

## Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	661ec80b-b956-4b0a-92bb-53046f4cfb4c
Uredba REACh	<a href="#">REACh Deklaracija</a>
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	<a href="#">Da</a>
Kina RoHS regulacija	<a href="#">RoHS Deklaracija Za Kinu</a>
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No

## Ugovorna garancija

Garancija	18 meseci
-----------	-----------