



Tehničke karakteristike proizvoda Karakteristike

PKZA203

Mureva system adapter - 1 utičnica - šuko - 16
A - 2P+E - 220V 50/60Hz

Osnovne informacije

Grupa proizvoda	Mureva
Tip proizvoda ili komponente	Adapter
Broj polova	2P + E
Standard utičnice	Nemački

Dopunske informacije

[in] nazivna struja	16 A
Broj utičnica	1
Materijal utikača, utičnice	Kućište: samogasivi polimer
Materijal kontakta	Pinovi: poniklovan mesing
Masa proizvoda	0,16 kg
Boja poklopca	Plava

Okruženje

Standardi	EN 50250 IEC 60309-1 IEC 60309-2
Ip stepen zaštite	IP20 conforming to IEC 60529
Ik stepen zaštite	IK08 conforming to EN 62262
Otpornost na vatru	850 °C u skladu sa IEC 60695-2-11

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5,6 cm
Package 1 Width	5,8 cm
Package 1 Length	11,5 cm
Package 1 Weight	160,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9,2 cm
Package 2 Width	26,8 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,738 kg
Unit Type of Package 3	S03
Number of Units in Package 3	40
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm

Package 3 Length	40,0 cm
Package 3 Weight	7,439 kg

Održivost ponude

Pakovanje bez plastike	Da
Pakovanje sa recikliranim kartonom	Da
SCIP broj	89350e0d-a4ac-4516-bf86-fdaed8a227fc
Uredba REACh	REACh Deklaracija
EU RoHS direktiva	Usaglašeno sa izuzecima
Bez žive	Da
Informacije o izuzeću od RoHS	Da
Kina RoHS regulacija	RoHS Deklaracija Za Kinu
Izjava o zaštiti okoline	Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Proizvod se mora odložiti na tržišta Evropske unije nakon posebnog sakupljanja otpada i nikada ne završiti u kanti za smeće
Povraćaj	No
Emisija ugljenika (kg CO2 eq.)	6

Ugovorna garancija

Garancija	18 meseci
-----------	-----------