





## Osnovne informacije

Tip proizvoda ili komponente	Motorna prigušnica
Kompatibilnost grupe proizvoda	Altivar 61Q Altivar 71Q Altivar 212 Altivar 71 Altivar Process ATV600 Altivar Process ATV900 Altivar 61
Specifične primene proizvoda	Izlazni filter
[in] nazivna struja	215 A

Kompatibilnost  
proizvoda

ATV61HD11N4  
ATV61HD15N4  
ATV61HD18N4  
ATV61HU22S6X  
ATV61HU30S6X  
ATV61HU40S6X  
ATV61HU55N4  
ATV61HU55S6X  
ATV61HU75N4  
ATV61HU75S6X  
ATV61WD11N4  
ATV61WD11N4C  
ATV61WD15N4  
ATV61WD15N4C  
ATV61WD18N4  
ATV61WD18N4C  
ATV61WU55N4  
ATV61WU55N4C  
ATV61WU75N4  
ATV61WU75N4C  
ATV71HD11N4  
ATV71HD11Y  
ATV71HD15N4  
ATV71HD18N4  
ATV71HU15S6X  
ATV71HU22S6X  
ATV71HU30S6X  
ATV71HU40S6X  
ATV71HU55N4  
ATV71HU55S6X  
ATV71HU75N4  
ATV71HU75S6X  
ATV71PD11N4Z  
ATV71PU55N4Z  
ATV71PU75N4Z  
ATV71WD11N4  
ATV71WD15N4  
ATV71WD18N4  
ATV71WU55N4  
ATV71WU75N4  
ATV212HU15N4  
ATV61HD15Y  
ATV61HD18Y  
ATV61HD22N4  
ATV61HD22Y  
ATV61HD30N4  
ATV61HD30Y  
ATV61HD37N4  
ATV61WD22N4  
ATV61WD22N4C  
ATV61WD30N4  
ATV61WD30N4C  
ATV61WD37N4  
ATV61WD37N4C  
ATV71HD15Y  
ATV71HD18Y  
ATV71HD22N4  
ATV71HD22Y  
ATV71HD30Y  
ATV71HD37N4  
ATV71WD30N4  
ATV71WD37N4  
ATV630 frekventni regulator - 2,2 kW, 500...690 V  
trofazno  
ATV630 frekventni regulator - 3 kW, 500...690 V  
trofazno  
ATV630 frekventni regulator - 4 kW, 500...690 V  
trofazno  
ATV630 frekventni regulator - 5,5 kW, 500...690 V  
trofazno  
ATV630 frekventni regulator - 7,5 kW, 500...690 V  
trofazno  
ATV630 frekventni regulator - 11 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 2,2 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 3 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 4 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 5,5 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 7,5 kW, 500...690 V  
trofazno  
ATV930 frekventni regulator - 11 kW, 500...690 V  
trofazno

Potrebna količina	3
Električna veza	Konektor M10

## Dopunske informacije

Maksimalna dužina kabla motora	150 M oklopljen kabl P motora 30...45 kW pri 200...240 V 1 300 M neoklopljen kabl P motora 30...45 kW pri 200...240 V 1 200 M oklopljen kabl P motora 5,5...18,5 kW pri 380...480 V 1 300 M neoklopljen kabl P motora 5,5...18,5 kW pri 380...480 V 1 150 M oklopljen kabl P motora 22...30 kW pri 380...480 V 1 300 M neoklopljen kabl P motora 22...30 kW pri 380...480 V 1 150 M oklopljen kabl P motora 45...75 kW pri 380...480 V 1 300 M neoklopljen kabl P motora 45...75 kW pri 380...480 V 1 150 M oklopljen kabl P motora 2,2...7,5 kW pri 500...600 V 1 250 M neoklopljen kabl P motora 2,2...7,5 kW pri 500...600 V 1 250 M oklopljen kabl P motora 2,2...7,5 kW pri 500...600 V 2 400 M neoklopljen kabl P motora 2,2...7,5 kW pri 500...600 V 2 100 M oklopljen kabl P motora 2,2...30 kW pri 500...690 V 2 150 M neoklopljen kabl P motora 2,2...30 kW pri 500...690 V 2 150 M oklopljen kabl P motora 11...30 kW pri 500...690 V 2 250 M neoklopljen kabl P motora 11...30 kW pri 500...690 V 2 150 M oklopljen kabl P motora 30...160 kW pri 500...690 V 1 250 M neoklopljen kabl P motora 30...160 kW pri 500...690 V 1 250 M oklopljen kabl P motora 30...160 kW pri 500...690 V 2 300 M neoklopljen kabl P motora 30...90 kW pri 500...690 V 2 400 M neoklopljen kabl P motora 90...160 kW pri 500...690 V 2 200 M oklopljen kabl P motora 37 kW pri 380...480 V 1 300 M neoklopljen kabl P motora 37 kW pri 380...480 V 1 200 M oklopljen kabl P motora 90 kW pri 380...480 V 1 300 m neoklopljen kabl P motora 90 kW pri 380...480 V 1
Dv/dt	500 V/μs maksimalno pri 400 V 750 V/μs maksimalno pri 500 V 1000 V/μs maksimalno pri 690 V
Termički gubici	430 W
Maksimalna izlazna frekvencija pogona	100 Hz
Temperatura okoline za rad	-10...50 °C
Masa proizvoda	15,5 kg



## Okruženje



Ip stepen zaštite	IP20 (sa setovima VW3A9612,613) IP00
Temperatura okoline za skladištenje	-25...70 °C

## Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	40,000 cm
Package 1 Width	60,000 cm
Package 1 Length	40,000 cm
Package 1 Weight	18,000 kg
Unit Type of Package 2	P06
Number of Units in Package 2	2
Package 2 Height	75,000 cm
Package 2 Width	60,000 cm
Package 2 Length	80,000 cm
Package 2 Weight	44,500 kg

## Održivost ponude

Pakovanje bez plastike	Ne
Pakovanje sa recikliranim kartonom	Ne
Uredba REACH	 <a href="#">REACH Deklaracija</a>
Bez SVHC-a REACH	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  <a href="#">EU RoHS deklaracija</a>

Bez toksičnih teških metala	Da
Bez žive	Da
Informacije o izuzeću od RoHS	 Da
Kina RoHS regulacija	 <a href="#">RoHS Deklaracija Za Kinu</a>
Povraćaj	No

### Ugovorna garancija

Garancija	18 meseci
-----------	-----------